

[All Products](#) / [Imaging Lenses](#) / [Variable Magnification Lenses](#) / [InfiniProbe™ Microscopes](#)

[See all 6 Products in Family](#)

InfiniProbe S-25 Right Angle Video Microscope (0-2.5X)

See More by [Infinity Photo-Optical Company](#)



Stock **#58-810** [CONTACT US](#)

⊖ 1 ⊕

A\$4,064.00

ADD TO CART

Qty 1+
A\$4,064.00

Volume Pricing
Request Quote

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
2.56mm

Horizontal Field of View, 2/3" Sensor:
3.52mm

Weight (g):
158.76

Type:
Long Distance Microscope

Primary Magnification PMAG:
0X - 2.5X

Maximum Sensor Format: 2/3"
Working Distance (mm): 32 - ∞
Mount: C-Mount
Style: Right Angle

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View