

Infrared Viewer (350-1550nm)



Infrared Viewer (350-1550nm), #36-084

Stock **#36-084** CLEARANCE 3-5 DAYS

⊖ 1 ⊕

A\$2,915.12

ADD TO CART

Qty 1+
A\$2,915.12
Volume Pricing
Request Quote

Get Product Downloads

Aperture (f/#):
f/1.4 - f/16

Operating Lifetime (hours):
>98-hours continuous

Focal Length FL (mm):
25.00

Magnification:
1:1 (Eyepiece)

Mount:
C-Mount

Operating Temperature (°C): -32 to +46
Resolution: 40 lp/mm
Dimensions (inches): 6.5 x 2.1 x 7.5
Spectral Response (nm): 350 - 1550
Weight (g): 595
Working Distance (inches): 7.87 to ∞
Power Requirement: (1) standard "C" cell alkaline battery
Field of View (°): 24
Focus Range: 0.2m - ∞
Filter Thread: M27 x 0.5

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View