

IR M46 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-646 3-5 DAYS



1



A\$267.20

ADD TO CART

Qty 1-9

A\$267.20

Qty 10+

A\$252.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):
200-784

Clear Aperture CA (mm):
41.00

Coating:
Hard Coated

Filter Thread:

M46 x 0.75
Color: IR
Center Wavelength CWL (nm): 850.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 160.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 48.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View