

Iris Mount for 37mm Outer Diameter Irises



Iris Mount for 70mm Outer Diameter Irises, #53-921



Stock **#53-919** 2 In Stock

-

1

+

A\$84^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$84.00 each
Qty 5-9	A\$74.24 each
Qty 10-25	A\$68.80 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
37.0	Compatible Iris Diameter (mm):
50.8	Outer Diameter (mm):
9.50	Thickness (mm):

Threading & Mounting

1/4-20	Mounting Threads:
6-32	Set Screw Thread:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details


• Multiple Iris Diameter Options Available

• Durable Anodized Aluminum Construction

• Set Screw Included

Iris Diaphragm Mbunts fit our most popular sizes of [Iris Diaphragms](#) and are constructed from durable black anodized aluminum. These mounts feature a variety of different English post mounting options, and each utilize an included set screw to ensure a secure fit.

Technical Information



Iris Diameter	A	B	C	D	E	F	G	H	Stock No.
19.8	30.8	19.8	6.1	6.35	2.5	4-40	15.1	8-32	#53-918
37.0	50.8	37.0	9.0	9.5	2.8	6-32	25.0	1/4-20	#53-919
53.0	66.0	53.0	9.9	9.5	3.0	6-32	32.7	1/4-20	#53-920
70.0	86.0	70.0	10.1	9.5	3.8	6-32	42.7	1/4-20	#53-921
21.0	32.0	21.0	6.2	9.5	3.2	4-40	15.7	8-32	#54-862
38.0	52.0	38.0	9.1	9.5	3.2	6-32	25.6	1/4-20	#54-863
54.0	67.0	54.0	8.9	9.5	3.8	6-32	33.2	1/4-20	#54-864
72.0	88.0	72.0	10.3	11.5	3.8	6-32	43.7	1/4-20	#54-865

