

Laser ZX20 660nm 100mW, 30°



Stock #19-434

3-5 DAYS



1



A\$2,160.00

ADD TO CART

Qty 1-9
A\$2,160.00
Qty 10+
A\$1,944.00
Volume Pricing
Request Quote

Get Product Downloads



Operating Temperature (°C):

-10 to +50

Output Power (mW):

100

Power Stability (%):

±3

Wavelength (nm):

660.00

Weight (g): 90
Laser Class - IEC: 3R
Housing Length (mm): 97
Housing Diameter (mm): 20
Storage Temperature (°C): -40 to +85
Bore Sighting (mrad): <0.8
Pointing Stability (µrad/°C): <10
Modulation Frequency (kHz): 400
Style: Homogeneous Line
Manufacturer: Z-Laser
Output Type: Free Space
Type of Laser: Diode
Laser Class - CDRH: IIIa
Color: Red
Connector: 5 pins, M12
Fan Angle (°): 30.00
Focus Range: 100mm to Collimation
Input Voltage (V): 5 - 30 DC

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View