

LS19 Ajustable Temples Wrap Around Frame, Laser Safety Glasses



Stock #17-639 3-5 DAYS

- 1 + **A\$435.20**

ADD TO CART

Qty 1-5

A\$435.20

Qty 6+

A\$391.68

Volume Pricing

[Request Quote](#)

Get Product Downloads

Color:
Grey

Optical Density OD (Average):
>5 @ 1025 - 1075nm
>6 @ 1035 - 1070nm
>7 @ 1045 - 1065nm
>2 @ 1450 - 1650nm

>3 @ 1651 - 1775nm
>4 @ 1776 - 3000nm
>5 @ 1980 - 2550nm
>5 @ 5200 - 11,000nm
>6 @ 9000 - 10,600nm

Visible Light Transmission VLT (%):
23

EN 207/208 Ratings:
DIRMLB5 @ 1025 - 1075nm, DIRMLB6 @ 1035 - 1070nm, D LB6 and IR LB7 and MLB7Y @ 1045 - 1065nm, DIR LB2 @ 1450 - 1650nm, DI LB3 and R LB3Y @ 1651 - 1775nm, DI LB4 and R LB3Y @ 1776 - 3000nm & 5200 - 11,000nm

Filter Material:
Polymer

Filter:
LS19

Style:
Adjustable Temples Wrap Around

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)