

# Lumenera INFINITY 3-3UR Microscopy Color Camera

See More by [Teledyne DALSA](#)



Stock #33-276 3-5 DAYS

- 1 +

A\$7,880.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1+                        |
| A\$7,880.00                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Video Output:  
USB 3.0

Type:  
Color Microscopy Camera

Manufacturer:  
Teledyne Lumenera

Mounting Threads:  
2 x 1/4-20 (Integrated into Housing)

|                                                                     |
|---------------------------------------------------------------------|
| <b>Image Buffer:</b><br>Not Specified                               |
| <b>Camera Family:</b><br>INFINITY                                   |
| <b>Model Number:</b><br>INFINITY3-3UR                               |
| <b>Imaging Sensor:</b><br>Sony ICX674                               |
| <b>Type of Sensor:</b><br>Progressive Scan CCD                      |
| <b>Type of Shutter:</b><br>Global                                   |
| <b>Camera Sensor Format:</b><br>2/3"                                |
| <b>Resolution (MegaPixels):</b><br>2.80                             |
| <b>Pixels (H x V):</b><br>1,936 x 1,456                             |
| <b>Pixel Size, H x V (µm):</b><br>4.54 x 4.54                       |
| <b>Sensing Area, H x V (mm):</b><br>8.79 x 6.61                     |
| <b>Frame Rate (fps):</b><br>53.00                                   |
| <b>Pixel Depth:</b><br>8/14 bit                                     |
| <b>Exposure Time:</b><br>23µs - 1.3s (video)                        |
| <b>Power Supply:</b><br>Power over USB                              |
| <b>Power Consumption (W):</b><br>6                                  |
| <b>GPIOs:</b><br>N/A                                                |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO)                  |
| <b>Dimensions (mm):</b><br>97.8 x 69.8 x 50.8 (excludes lens mount) |
| <b>Weight (g):</b><br>340                                           |
| <b>Mount:</b><br>C-Mount                                            |
| <b>Housing:</b><br>Full                                             |
| <b>Interface Port Orientation:</b><br>Side Panel                    |
| <b>Dynamic Range (dB):</b><br>68.8                                  |
| <b>Operating Temperature (°C):</b><br>0 to +50                      |
| <b>Storage Temperature (°C):</b><br>-30 to +70                      |
| <b>GPIO Connector Type:</b><br>8-pin Hirose (MRX)                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br>Compliant                                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |