

Lumenera INFINITY 3-6UR Microscopy Color Camera

See More by [Teledyne DALSA](#)



Stock #33-289 3-5 DAYS

- 1 +

A\$9,600.00

ADD TO CART

Qty 1+
A\$9,600.00

Volume Pricing
Request Quote

Get Product Downloads

Video Output:
USB 3.0

Type:
Color Microscopy Camera

Manufacturer:
Teledyne Lumenera

Mounting Threads:
2 x 1/4-20 (Integrated into Housing)

Image Buffer: Not Specified
Camera Family: INFINITY
Model Number: INFINITY3-6UR
Imaging Sensor: Sony ICX694
Type of Sensor: Progressive Scan CCD
Type of Shutter: Global
Camera Sensor Format: 1"
Resolution (MegaPixels): 6.00
Pixels (H x V): 2,752 x 2,192
Pixel Size, H x V (µm): 4.54 x 4.54
Sensing Area, H x V (mm): 12.49 x 9.95
Frame Rate (fps): 27.00
Pixel Depth: 8/14 bit
Exposure Time: 23µs - 1.79s (video)
Power Supply: Power over USB
Power Consumption (W): 6
GPIOs: N/A
Synchronization: Hardware Trigger (GPIO)
Dimensions (mm): 97.8 x 69.8 x 50.8 (excludes lens mount)
Weight (g): 395
Mount: C-Mount
Housing: Full
Interface Port Orientation: Side Panel
Dynamic Range (dB): 68.6
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +70
GPIO Connector Type: 8-pin Hirose (MRX)

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View