

[See all 8 Products in Family](#)

M34.0 x 0.5 Male to T-Mount Female Step-Up Adapter



M27.0 x 0.5 to T-Mount Step-Up Adapter, #12-481

Stock **#12-483** **3 In Stock**

A\$54⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$54.80 each
Qty 10-25	A\$49.44 each
Need More?	Request Quote

Product Downloads

General

Filter Sold Separately **Note:**

Filter Adapter **Type:**

Thread Adapter **Function:**

Physical & Mechanical Properties

Clear Aperture CA (mm):

31.0

Outer Diameter (mm):

48.0

Total Thickness with Thread (mm):

8.0

Threading & Mounting

Thread Type:

T-Mount to M34.0 x 0.5

Inner Thread:

M42 x 0.75 (T-Mount)

Mount Thickness (mm):

5.5

Outer Thread:

M34.0 x 0.5

Regulatory Compliance

Certificate of Conformance:

[View](#)

Reach 240:

[Compliant](#)

Product Details

- Integrate C and T-Mount Components into Imaging Systems
- Compatible with M22.5 to M40.5 Machine Vision Threads
- Step-Up Design Prevents Vignetting

Machine Vision Adapters for C and T-Mount Components facilitate integration of various components into imaging systems. Polarizers, beamsplitters, or any other C or T-Mount component can be coupled to a standard machine vision thread via these adapters. Additionally, unmounted optical components including filters can be mounted in our [C-Mount or T-Mount Circular Optic Mounts](#) for easy integration. Compatible machine vision threads range from M22.5 to M40.5. The step-up design prevents vignetting.