

M37.5 x 0.50 Machine Vision Mounted Linear Glass Polarizing Filter



Stock #21-681 3-5 DAYS

- 1 + **A\$122.40**

ADD TO CART

Qty 1-9
A\$122.40
Qty 10+
A\$117.28
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
32.50

Coating:
Hardcoated

Diameter (mm):
39.50

Extinction Ratio:
3000:1

Filter Thread: M37.5 x0.50
Surface Quality: 40-20
Type: Mounted Imaging Filter
Construction: Black Anodized Aluminum
Wavelength Range (nm): 400 - 700
Mount Thickness Including Threads (mm): 9.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View