

M46 x 0.75 Mounted UV/VIS Cut-Off, IR Pass Filter (R-72)



Stock **#64-887** 3-5 DAYS

-

1

+

A\$124.00

ADD TO CART

Qty 1-9
A\$124.00
Qty 10+
A\$114.24
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):

42.0

Coating Specification:

R_{avg} ≤1.75% @400 - 700nm

Filter Thread:

M46 x0.75

Cut-Off Wavelength (nm):

2,750.00

Cut-On Wavelength (nm): 720.00
Glass/Filter Number: R-72
Index of Refraction n_d: 1.55
Mount Thickness (mm): 6.4 ±0.1
Mount Thickness Including Threads (mm): 7.1
Note: AR Coating: Both Surfaces Single Layer MgF ₂
Outer Diameter (mm): 48.0
Substrate:  Hoya R-72
Substrate Thickness (mm): 2.5
Surface Quality: 80-50
Thickness with Mount (mm): 5.0
Type: Mounted Imaging Filter

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View