

M67 x 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock #64-900 3-5 DAYS



1



A\$99.20

ADD TO CART

Qty 1-9

A\$99.20

Qty 10+

A\$92.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
62.00

Coating:
Uncoated

Diameter (mm):
70.00 +0/-0.2

Extinction Ratio:

Approx. 19:1 at 400nm
Approx. 200:1 at 500nm
≥2700:1 at 550-650nm
Approx. 600:1 at 700nm

Filter Thread:
M67 x0.75

Substrate: ☐
Float Glass

Operating Temperature (°C):
-15 to +70

Polarization:
95% Efficiency

Transmission (%):
Single: 30
Crossed: 0.15

Type:
Mounted Imaging Filter

Construction:
Dichroic

Mount Thickness (mm):
9 ±0.1

Wavelength Range (nm):
400 - 700

Mount Thickness Including Threads (mm):
11

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)