

M72 x 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock **#52-560** CLEARANCE 3-5 DAYS



1



A\$33.52

ADD TO CART

Qty 1+

A\$33.52

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
68.00

Coating:
Uncoated

Diameter (mm):
74.50

Extinction Ratio:
Approx. 19:1 at 400nm
Approx. 200:1 at 500nm
≥2700:1 at 550-650nm
Approx. 600:1 at 700nm

Filter Thread: M72 x0.75
Substrate: ☐ Float Glass
Operating Temperature (°C): -15 to +70
Polarization: 95% Efficiency
Transmission (%): Single: 30 Crossed: 0.15
Type: Mounted Imaging Filter
Construction: Dichroic
Mount Thickness (mm): 9
Wavelength Range (nm): 400 - 700
Mount Thickness Including Threads (mm): 11

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View