

1/4-20 Mounting Adapter for Stingray

See More by [Allied Vision](#)



Stock **#59-157** **1 In Stock**

-

1

+

A\$38⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$38.00 each
Need More?	Request Quote

Product Downloads

General

Camera Accessory

Type:

Hardware & Interface Connectivity

Power Supply:

Power over FireWire, or with Power Supply Sold Separately.

USA: [#15-281](#)

Europe: [#15-281](#)

Japan: [#15-281](#)

China: [#15-281](#)

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Excellent Price/Performance Ratio
- High bit-depth (14-bit or 8-bit output, user-selectable)
- VGA(640 x 480) – 5MP Resolutions Available

The Allied Vision Stingray FireWire.b Camera is a part of the Allied Vision Stingray camera family, which offers high-performance cameras that utilize a high-speed IEEE-1394-b interface at an economical price. Using Sony CCD sensors, 14-bit depth output, and on-board SmartFeatures allows for greater flexibility in demanding image applications. Every member of the Stingray family has high sensitivity and is available in color or monochrome versions. The Allied Vision Stingray FireWire.b Camera is compatible with PC (including VMD) or Linux environments. Each camera includes a firewire cable. Drive and SDK can be [downloaded](#) from Allied Vision website. Optional 1/4-20 mounting adapter [#59-157](#), 12-pin trigger I/O cable, and laptop FireWire card are available.