

40mm PetzVex™ MikroMak™ CINE Prime Probe Lens



MikroMak™ PetzVex™ Prime Probe Lenses



Stock **#17-660** 1 In Stock

-

1

+

A\$5,544⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$5,544.00 each
Need More?	Request Quote

Product Downloads

General	
Variable Magnification Lens	Type:
Physical & Mechanical Properties	
185.50	Length (mm):
48.00	Maximum Diameter (mm):

Optical Properties	
43.30	Maximum Image Circle (mm):
0X - 1.75X	Primary Magnification PMAG:
16 - ∞	Working Distance (mm):
Sensor	
35mm (43.3mm Image Circle)	Maximum Sensor Format:
Threading & Mounting	
M42 x 0.75 (T-Mount)	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Arthouse Design for the Petzval Look
- Use from Macro to Infinity with Excellent Sharpness over Depth of Field
- Ideal for Cinema Production and Creative Photographic Applications
- [MikroMak™ Prime Probe Lenses](#) Also Available

MikroMak™ PetzVex™ Prime Probe Lenses, part of Infinity Photo-Optical Company's line of Nelsonian™ Optics, produce the Petzval Arthouse look of soft image edges with sharpness over great depth in the center of the image, drawing attention to the subject. Like other members of the [MikroMak™ Prime Probe family](#), when set to infinity, everything up to a close proximity of the lens is automatically in focus. The knurled focus ring can then be used to adjust the focus of the lens to the micro or macro range, indicated by magnification markings on the lens body. MikroMak™ Prime PetzVex™ Prime Probe Lenses provide the flexibility required for creative story telling in photography and cinema production applications while providing the high performance required for industrial and laboratory settings.

PetzVex™ models are available in 40mm and 50mm designs. A suite of accessories including adapters to C-Mount, L-Mount, and Sony mounts, mounting solutions, and spacers are available; see each specific accessory for more information.

Visit the [Infinity Photo-Optical Cinema Products](#) brand page to learn more about these products!