

Mounted M22.5 x 0.5 Threaded - Red Filter



Stock #46-539 3-5 DAYS

-

1

+

A\$76.00

ADD TO CART

Qty 1-9

A\$76.00

Qty 10+

A\$70.56

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
18.5

Filter Thread:
M22.5 x 0.50

Color:
Red

Cut-On Wavelength (nm):
600.00

Glass/Filter Number: R-60
Index of Refraction n_d: 1.53
Note: AR Coating: MgF₂
Outer Diameter (mm): 24.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.0
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.0
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya R-60 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View
