

Mounted M22.5 x 0.5 - UV Cut-Off Filter



Mounted UV Filters

Stock **#58-647** 3-5 DAYS

- 1 + **A\$129.60**

ADD TO CART

Qty 1-9
A\$129.60
Qty 10+
A\$125.68
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 18.5
Cut-On Wavelength (nm): 390.00
Filter Thread: M22.5 x0.50
Glass/Filter Number:

L-39
Substrate: Hoya L-39
Operating Temperature (°C): -15 to +70
Coating: Uncoated
Color: Clear
Outer Diameter (mm): 24.0
Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Type: Mounted Imaging Filter
Mount Thickness (mm): 5.2 ±0.3
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 4 - 6λ
Substrate Thickness (mm): 2.5
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View