

Mounted M43 x 0.75 - UV Cut-Off Filter



Mounted UV Filters

Stock **#54-040** 3-5 DAYS



1



A\$88.00

ADD TO CART

Qty 1-9

A\$88.00

Qty 10+

A\$82.88

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
39.5

Cut-On Wavelength (nm):
390.00

Filter Thread:
M43 x0.75

Glass/Filter Number:

L-39
Substrate: Hoya L-39
Operating Temperature (°C): -15 to +70
Coating: AR Coated
Color: Clear
Outer Diameter (mm): 45.0
Thickness with Mount (mm): 4.50
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Type: Mounted Imaging Filter
Coating Specification: R _{avg} >2% @ 400 - 700nm
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View