

[See all 17 Products in Family](#)

## Mounted M52 x 0.75 - UV Cut-Off Filter



Mounted UV Filters

Stock #54-044 **12 In Stock**

⊖ 1 ⊕ A\$113<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-9	A\$113.60 each
Qty 10-25	A\$102.40 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Mounted Imaging Filter **Type:**

#### Physical & Mechanical Properties

47.0 **Clear Aperture CA (mm):**

54.0 **Outer Diameter (mm):**

**Thickness with Mount (mm):**

4.50

Thickness (mm):

2.00 ±0.2

## Optical Properties

Cut-On Wavelength (nm):

390.00

Glass/Filter Number:

L-39

Substrate:

Hoya L-39

Coating:

AR Coated

Color:

Clear

Surface Quality:

80-50

Coating Specification:

R<sub>avg</sub> >2% @ 400 - 700nm

Wavelength Range (nm):

350 - 2200

Surface Flatness (P-V):

4 - 6λ

## Threading & Mounting

Filter Thread:

M52 x0.75

## Environmental & Durability Factors

Operating Temperature (°C):

-15 to +70

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Blocks UV and Transmits Visible
- Ideal as Dust or Protective Covers for Camera Sensors

Mounted UV Filters are offered with standard photographic and lens filter mount threads. These filters are ideal for applications where UV light needs to be blocked and visible light passed. The mounted clear aperture is 5mm less than the mount diameter. The maximum outer diameter is 2mm greater than the mount diameter, except for the 62mm and 72mm, which are 3mm larger. Mounted UV Filters are clear in color and non-rotatable.

## Technical Information

