

Mounted M72 x 0.75 Threaded - Green Filter



Stock **#46-536** [CONTACT US](#)

- 1 + **A\$110.40**

ADD TO CART

Qty 1-9
A\$110.40
Qty 10+
A\$102.40
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
68.0

Filter Thread:
M72 x 0.75

Color:
Green

Cut-Off Wavelength (nm):
550.00

Cut-On Wavelength (nm): 520.00
Glass/Filter Number: G-533
Index of Refraction n_d: 1.54
Mount Thickness (mm): 4.9 ±0.1
Mount Thickness Including Threads (mm): 7.4
Note: AR Coating: MgF ₂
Outer Diameter (mm): 75.0
Substrate:  Colored Glass
Substrate Thickness (mm): 2.5
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.5
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya G-533 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View