

Mounted M77 x 0.75 - UV Cut-Off Filter



Mounted UV Filters

Stock **#64-894** 3-5 DAYS

- 1 +

A\$136.00

ADD TO CART

Qty 1-9
A\$136.00
Qty 10+
A\$125.44
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 72.0
Cut-On Wavelength (nm): 350.00
Filter Thread: M77 x0.75
Glass/Filter Number:

Optical Glass
Substrate: Optical Glass
Operating Temperature (°C): -15 to +70
Coating: Multi-coated
Color: Clear
Outer Diameter (mm): 80.0 +0/-0.2
Thickness with Mount (mm): 4.30
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.1
Type: Mounted Imaging Filter
Coating Specification: R_{avg} >2% @ 500 - 700nm
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 4 - 6λ
Mount Thickness Including Threads (mm): 6.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View