

Mounted Window for 1030nm, 0.80 NA, aplanoXX Aplan Objective

See More by [AdlOptica](#)



Mounted Window

Stock **#19-495** 3-5 DAYS

-

1

+

A\$481.60

ADD TO CART

Qty 1+

A\$481.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
8

Design Wavelength DWL (nm):
515, 1030

Diameter (mm):
29.50

Model Number:
WnDow in Holder L9333.06 (+D12_515/1030)

Length (mm):

4.40
Type: Mounted Window
Note: Protective window for #19-491
Wavelength Range (nm): 510 - 545, 1020 - 1100
Damage Threshold, By Design: ☐ 25 mJ @ 5ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant