

[See all 11 Products in Family](#)

## Needle Nose Style, Soft Jaw Pliers



Stock #59-903 **8 In Stock**

- 1 + A\$73<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$73.60 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

### Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

### Product Details

- Non-Marring Cushioned Tips
- Screw-In Cushioned Tip Design

- Replacement Tips Available

The slip joint design utilized in these pliers is ideal for handling optics, camera-lens assemblies, and other delicate components. Jaw openings range from 1" to 2.75" (dependent on model). Jaws feature screw-in plastic cushions to protect fine knurling and delicate finishes. Tool body is laminated and handles are covered with rolled vinyl to ensure proper grip.

---

;