

NUV M77 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-400 3-5 DAYS



1



A\$633.60

ADD TO CART

Qty 1-9

A\$633.60

Qty 10+

A\$601.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):

200-250, 400-650

Clear Aperture CA (mm):

73.00

Coating:

Hard Coated

Filter Thread:

M77 x0.75
Color: NUV
Center Wavelength CWL (nm): 324.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 105.00
Mount Thickness (mm): 6.0
Mount Thickness Including Threads (mm): 8.3
Outer Diameter (mm): 80.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View