

OD 3.0 VIS, 12.5mm Dia. Non-Reflective ND Filter



Non-Reflective Neutral Density (ND) Filters

Stock #63-385 [CONTACT US](#)



1



A\$176.00

ADD TO CART

Qty 1-10

A\$176.00

Qty 11+

A\$158.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 ±0.10

Optical Density OD (Average):
3.0

Substrate: ☐
[B270](#)

Coating: Non-Reflective ND
Reflection (%) : ≤1.5
Surface Quality : 60-40
Thickness (mm) : 1.50
Thickness Tolerance (mm) : ±0.1
Transmission (%) : 0.10
Transmission Tolerance (%) : ±0.05
Type : Neutral Density Filter
Parallelism (arcmin) : <5
Clear Aperture (%) : 90.00
Surface Accuracy : 2λ
Wavelength Range (nm) : 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
