


SCHOTT OG-570, 50mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#66-090** 3-5 DAYS

-

1

+

A\$140.80

ADD TO CART

Qty 1-10
A\$140.80
Qty 11+
A\$124.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
50.00

Cut-Off Position λ_c (nm):
570±6

Cut-On Wavelength (nm):

570.00
Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT OG570
Coating: Uncoated
Color: Orange
Passband Limit 1 λ_{p1} (nm): 640.00
Spectral Transmittance t_p (%): 93.00
Stopband Limit λ_s (nm): 500.00
Surface Quality: 80-50
Transformation Temperature (°C): 510.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View