

Olympus UPLFLN 60X Objective

See More by [Olympus](#)



Olympus UPLFLN 60X Objective

Stock **#86-822** 3-5 DAYS

− 1 +

A\$5,467.20

ADD TO CART

Qty 1+
A\$5,467.20

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.11 - 0.23

Field of View (mm):
0.44

Focal Length FL (mm):
3.00

Model Number:
1-U2B5312

Length excluding Threads (mm):

44.70
Magnification: 60X
Maximum Diameter (mm): 31
Numerical Aperture NA: 0.90
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (μm): 0.36
Depth of Field (μm): 0.34
Working Distance (mm): 0.20
Weight (g): 156
Wavelength Range (nm): 380 - 900
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--