

Olympus UPLXAPO 20X Objective

See More by [Olympus](#)



Olympus UPLXAPO 20X Objective, #14-907

Stock **#14-907** 3-5 DAYS

⊖ 1 ⊕

A\$5,862.40

ADD TO CART

Qty 1+
A\$5,862.40

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
1.33

Focal Length FL (mm):
9.00

Model Number:
UPLXAPO20X

Length excluding Threads (mm):

44.45
Magnification: 20X
Maximum Diameter (mm): 28
Numerical Aperture NA: 0.80
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (μm): 0.42
Depth of Field (μm): 0.43
Working Distance (mm): 0.61
Weight (g): 149
Note: Spring-loaded
Wavelength Range (nm): 300 - 1000
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45.06
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--