

Power Supply for 0.5-0.8mW HeNe Laser, 24 VDC, Bare Wire Leads



L28 Series with CDRH Delay HeNe Laser Power Supply

Stock #11-383 3-5 DAYS

- 1 + **A\$529.60**

ADD TO CART

Qty 1+

A\$529.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (inches):
4.00 x 1.50 x 1.00

Type:
OEM

Output Voltage (V):
1250

Output Current (mA):
4

Compatible Laser Models:
[1108](#), [1108P](#), [1107](#), [1107P](#)

Output Power (W): 5
Input Current (A): 0.95 (Max. Current Draw)
Connector: High Voltage Alden Connector
Input Voltage (V): 22-30 DC
Model Number: L28 Series
Compatible Laser Stock Number: #62-714 , #62-715 , #62-716 , #62-717
Features: CDRH Delay (3-5 seconds)

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View