

[See all 43 Products in Family](#)

## Power Supply for 2mW HeNe Laser, AC, US Plug



Benchtop Power Supply, AC Input (Front)



Stock **#11-389** **6 In Stock**

- 1 + A\$1,320.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$1,320.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads



### General

Type:  
Benchtop

Compatible Laser Models:  
[1122](#), [1122P](#)

Model Number:  
SL92 Series

Compatible Laser Stock Number:  
[#62-720](#), [#62-721](#)

Turn Key, CDRH Delay (3-5 seconds) **Features:**

## Physical & Mechanical Properties

9.00 x 5.50 x 2.38 **Dimensions (inches):**

## Electrical

11.7 **Output Power (W):**

0.55/0.32 **Input Current (A):**

## Hardware & Interface Connectivity

1800 **Output Voltage (V):**

6.5 **Output Current (mA):**

High Voltage Alden Connector **Connector:**

100/110/220 (AC) **Input Voltage (V):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

**Note:** Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

## Technical Information

### Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

