

Preloaded Norland Optical Adhesive NOA 89H Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#17-372** [CONTACT US](#)

− 1 +

A\$60.80

ADD TO CART

Qty 1-4
A\$60.80
Qty 5+
A\$57.12
Volume Pricing
Request Quote

Get Product Downloads

Size (oz):
0.34

Glass Bonding:
Excellent

Metal Bonding:
Good

Plastic Bonding: Fair
Viscosity (cps): 15 - 20
Durability: Soft
Index of Refraction n_d: 1.51
Norland Number: 89H
Shelf Life: 4 months
Type: Barrel
Typical Applications: Bonding glass to glass
Note: Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.
Absorption Range (nm): 310 - 395
Bonding Type: Glass to Glass
Energy for Full Cure (J/cm²): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
