

Hoya R60 (600nm), 25.4mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #66-054 3-5 DAYS

⊖ 1 ⊕

A\$70.40

ADD TO CART

Qty 1-10

A\$70.40

Qty 11+

A\$62.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40

Cut-Off Position λ_c (nm):
600±6

Cut-On Wavelength (nm):
600.00 ±6

Density (g/cm³): 2.69
Glass/Filter Number: Hoya R60
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Red
Surface Quality: 80-50
Transformation Temperature (°C): 560
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P _d : 0.92
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View