

Red Orange, Ethernet High Intensity Coaxial Spot Light

See More by [Advanced Illumination](#)



Stock #21-360 3-5 DAYS

- 1 + **A\$856.00**

ADD TO CART

Qty 1+

A\$856.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red Orange

Model Number:
SL162-625C1

Operating Temperature (°C):
0 to +60

Wavelength (nm):
625.00

Weight (g): 85.1
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of LEDs: 1
Length of Cable (m): 2
Type of Illumination: LED Illuminator
Note: Required Controller #18-645 ; Required Power Supply #66-855
Manufacturer: Advanced Illumination
Geometry: Spot Light
Illumination Mode: Constant, Pulsed, Gated

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
