


SCHOTT RG-665, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#45-070** 3-5 DAYS

- 1 +

A\$62.00

ADD TO CART

Qty 1-10
A\$62.00
Qty 11+
A\$60.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.40

Cut-Off Position λ_c (nm):
665±6

Cut-On Wavelength (nm):

665.00
Density (g/cm³): 2.77
Glass/Filter Number: SCHOTT RG665
Coating: Uncoated
Color: Red
Passband Limit 1 λ_{p1} (nm): 750.00
Spectral Transmittance t_p (%): 96.00
Stopband Limit λ_s (nm): 580.00
Surface Quality: 80-50
Transformation Temperature (°C): 527.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d : 0.91
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View