


SCHOTT RG-850, 12.5mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#54-664** 3-5 DAYS

-

1

+

A\$51.20

ADD TO CART

Qty 1-10
A\$51.20
Qty 11+
A\$44.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Cut-Off Position λ_c (nm):
850±9

Cut-On Wavelength (nm):

850.00
Density (g/cm³): 2.93
Glass/Filter Number: SCHOTT RG850
Coating: Uncoated
Color: Black
Passband Limit 1 λ_{p1} (nm): 1200.00
Passband Limit 2 λ_{p2} (nm): 1200.00
Spectral Transmittance t_p (%): 97.00
Stopband Limit λ_s (nm): 700.00
Surface Quality: 80-50
Transformation Temperature (°C): 554.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: IR
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d : 0.91
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Compliant