

# SCHOTT RG9, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#84-903** 3-5 DAYS

− 1 +

**A\$44.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| A\$44.00                      |
| Qty 11+                       |
| A\$42.80                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

Diameter (mm):  
25.40

Cut-On Wavelength (nm):  
726.00

Density (g/cm³):

|                                                    |
|----------------------------------------------------|
| 2.58                                               |
| Full Width-Half Max FWHM (nm):<br>315.00           |
| Glass/Filter Number:<br><a href="#">SCHOTT RG9</a> |
| Coating:<br>Uncoated                               |
| Color:<br>Black                                    |
| Index of Refraction $n_d$ :<br>1.52                |
| Surface Quality:<br>80-50                          |
| Transformation Temperature (°C):<br>519            |
| Thickness (mm):<br>3.00 ±0.2                       |
| Type:<br>Longpass Filter                           |
| Wavelength:<br>IR                                  |
| Dimensional Tolerance (mm):<br>±0.38               |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Exempt</a>                |
| Reach 224:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |