

## Rodagon 50mm FL - Video Lens



Lens + Modular Focus Tube + Basler Line Scan Camera

Stock **#14-700** [CONTACT US](#)



1



**A\$832.00**

ADD TO CART

Qty 1+

A\$832.00

Volume Pricing

[Request Quote](#)

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

**Field of View @ Min Working Distance (mm):**  
17.3

**Iris Option:**  
Variable

**Length (mm):**  
43.50

**Horizontal Field of View, 1/2" Sensor:**  
6.8°

|                                                                                                                                                                                                                                                                                              |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Filter Thread:</b><br>M40.5 x 0.50                                                                                                                                                                                                                                                        |
| <b>Maximum Diameter (mm):</b><br>50.0                                                                                                                                                                                                                                                        |
| <b>Maximum Image Circle (mm):</b><br>40.00                                                                                                                                                                                                                                                   |
| <b>Note:</b><br>Requires Leica Lens Adapter M39 x 1/26" <a href="#">#14-705</a> ,<br>Modular Focus Tube <a href="#">#14-707</a> , and a lens mount<br>adapter ( <a href="#">C-Mount</a> , <a href="#">F-Mount</a> , <a href="#">T-Mount</a> , <a href="#">SLR</a> , or <a href="#">M72</a> ) |
| <b>Type:</b><br>Fixed Focal Length Lens                                                                                                                                                                                                                                                      |
| <b>Focal Length FL (mm):</b><br>50.00                                                                                                                                                                                                                                                        |
| <b>Primary Magnification PMAG:</b><br>0.37X                                                                                                                                                                                                                                                  |
| <b>Maximum Sensor Format:</b><br>40mm (Image Circle)                                                                                                                                                                                                                                         |
| <b>Working Distance (mm):</b><br>155 - ∞                                                                                                                                                                                                                                                     |
| <b>Mount:</b><br>Adapter Required                                                                                                                                                                                                                                                            |
| <b>Aperture (f/#):</b><br>f/2.8 - f/16                                                                                                                                                                                                                                                       |
| <b>Lens Wavelength Range:</b><br>VIS                                                                                                                                                                                                                                                         |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |

---