

Hoya RT830 (IR) 25mm Square, Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#46-086** [CONTACT US](#)

[-](#) 1 [+](#)

A\$100.80

ADD TO CART

Qty 1-10

A\$100.80

Qty 11+

A\$89.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
25.0 x 25.0

Center Wavelength CWL (nm):
830.00

Density (g/cm³): 2.75
Full Width-Half Max FWHM (nm): 260.00
Glass/Filter Number: Hoya RT830
Substrate: ☐ Colored Glass
Length (mm): 25.00
Coating: Uncoated
Color: Black
Surface Quality: 80-50
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: IR
Width (mm): 25.00
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View