

TECHSPEC[®]

S-Mount Kinematic Mount (2-Screw Adjustment)



S-Mount Kinematic Mount (2-Screw Adjustment) (#11-132)

Stock #11-132

3-5 DAYS



1



A\$180.80

ADD TO CART

Qty 1-49

A\$180.80

Qty 50+

A\$171.84

Volume Pricing

[Request Quote](#)

Get Product Downloads

Mounting Threads:
M4

Thickness (mm):
19.60

Travel (mm):
No Z-Axis Translation

Type:

Tube Mount
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 7.0
Pointing Accuracy (μrad): 1.3
Adjustment Screw Pitch (mm): 0.20
Thread Type: S-Mount
Number of Adjustment Screws: 2
Aperture Size: M12 x0.5
Height (mm): 23.5
Function: Kinematic (Tip-Tilt)
Compatible Post: M4 x0.7

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View