

SCHOTT BG36, 12.5mm Dia., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-402** 3-5 DAYS

- 1 +

A\$115.20

ADD TO CART

Qty 1-10
A\$115.20
Qty 11+
A\$100.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.50

Density (g/cm³):
3.59

Glass/Filter Number:

SCHOTT BG36

Coating:
Uncoated

Color:
Clear

Index of Refraction n_d :
1.69

Surface Quality:
60-40

Transformation Temperature (°C):
657

Thickness (mm):
3.00 ±0.2

Type:
Bandpass Filter

Wavelength:
UV-IR

Bevel:
Protective as needed

Regulatory Compliance

Certificate of Conformance:
[View](#)