

# SCHOTT BG38, 50mm Sq., 2mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock #14-416 3-5 DAYS

- 1 +

A\$140.80

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| A\$140.80                     |
| Qty 11+                       |
| A\$124.80                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Dimensions (mm):  
50.0 x 50.0

Center Wavelength CWL (nm):  
470.00

Density (g/cm<sup>3</sup>):

|                                                            |
|------------------------------------------------------------|
| 2.66                                                       |
| <b>Glass/Filter Number:</b><br><a href="#">SCHOTT BG38</a> |
| <b>Length (mm):</b><br>50.00                               |
| <b>Coating:</b><br>Uncoated                                |
| <b>Color:</b><br>Blue-Green                                |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.53       |
| <b>Surface Quality:</b><br>60-40                           |
| <b>Transformation Temperature (°C):</b><br>482             |
| <b>Thickness (mm):</b><br>2.00 ±0.2                        |
| <b>Type:</b><br>Bandpass Filter                            |
| <b>Wavelength:</b><br>VIS                                  |
| <b>Width (mm):</b><br>50.00                                |
| <b>Bevel:</b><br>Protective as needed                      |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |