

SCHOTT BG39, 50mm Sq., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock #14-420 3-5 DAYS

- 1 +

A\$140.80

ADD TO CART

Qty 1-10
A\$140.80
Qty 11+
A\$124.80
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Center Wavelength CWL (nm):
507.00

Density (g/cm³):

2.74
Glass/Filter Number: SCHOTT BG39
Length (mm): 50.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d : 1.54
Surface Quality: 60-40
Transformation Temperature (°C): 322
Thickness (mm): 3.00 ±0.2
Type: Bandpass Filter
Wavelength: VIS
Width (mm): 50.00
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View