

SCHOTT BG7, 50mm Sq., 1mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock #14-406 3-5 DAYS

- 1 +

A\$140.80

ADD TO CART

Qty 1-10
A\$140.80
Qty 11+
A\$124.80
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Center Wavelength CWL (nm): 488.00
Density (g/cm³):

2.61
Glass/Filter Number: SCHOTT BG7
Length (mm): 50.00
Coating: Uncoated
Color: Deep Blue
Index of Refraction n_d: 1.52
Surface Quality: 60-40
Transformation Temperature (°C): 468
Thickness (mm): 1.00 ±0.1
Type: Bandpass Filter
Wavelength: UV-VIS
Width (mm): 50.00
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View