

SCHOTT GG455, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock #16-411

3-5 DAYS

-

1

+

A\$51.20

ADD TO CART

Qty 1-10
A\$51.20
Qty 11+
A\$44.80
Volume Pricing
Request Quote

Get Product Downloads
Diameter (mm): 12.50
Cut-On Wavelength (nm): 455.00 ±6
Density (g/cm³):

2.56
Glass/Filter Number: SCHOTT GG455
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 530
Passband Limit 2 λ_{p2} (nm): 700
Index of Refraction n_d : 1.52
Spectral Transmittance t_p (%): 92
Stopband Limit λ_s (nm): 390
Surface Quality: 60-40
Transformation Temperature (°C): 529
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
