


SCHOTT GG495, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock #16-413 3-5 DAYS



1



A\$51.20

ADD TO CART

Qty 1-10

A\$51.20

Qty 11+

A\$44.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
495.00 ±6

Density (g/cm³):

2.56
Glass/Filter Number: SCHOTT GG495
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 560
Index of Refraction n_d: 1.52
Spectral Transmittance t_p (%): 92
Stopband Limit λ_s(nm): 430
Surface Quality: 60-40
Transformation Temperature (°C): 535
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
--