

SCHOTT KG5, 25mm Dia., 1mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock #19-333 3-5 DAYS

- 1 +

A\$56.00

ADD TO CART

Qty 1-10

A\$56.00

Qty 11+

A\$49.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00

Density (g/cm³):
2.53

Glass/Filter Number:
[SCHOTT KG5](#)

Substrate: Heat Absorbing Glass
Operating Temperature (°C): 300 Maximum
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 565
Thickness (mm): 1.00 ±0.1
Type: IR Cut-Off Filter
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Wavelength Range (nm): 300 - 2700
Bevel: Protective as needed

Regulatory Compliance

Reach 223: Compliant
Certificate of Conformance: View