

SCHOTT NG9, 165 x 165mm, 4.5mm Thick, Matte Colored Glass Filter Plate

See More by [SCHOTT Optical Components](#)



SCHOTT NG Glass (glass color will vary by product specification)

Stock **#16-924** 3-5 DAYS

-

1

+

A\$452.80

ADD TO CART

Qty 1-10
A\$452.80
Qty 11+
A\$408.00
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
165.0 x 165.0 +3.0/-0.0

Density (g/cm³):
2.45

Glass/Filter Number:
[SCHOTT NG9](#)

Length (mm): 165.00
Coating: Uncoated
Color: Gray
Index of Refraction n_d: 1.51
Transformation Temperature (°C): 470
Thickness (mm): 4.50 ±0.5
Type: Neutral Density Filter
Wavelength: VIS
Width (mm): 165.00
Edges: Break Edges
Reflection Factor P_d: 0.92

Regulatory Compliance

Certificate of Conformance: View
--