

SCHOTT NG9, 2.6 OD, 50mm Sq., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-058** 3-5 DAYS

- 1 + **A\$148.80**

ADD TO CART

Qty 1-10
A\$148.80
Qty 11+
A\$131.20
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):
2.6 ±0.07 @ 546nm

Glass/Filter Number:
[SCHOTT NG9](#)

Length (mm):

50.00
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 470
Thickness (mm): 1.90
Thickness Tolerance (mm): (nominal)
Transmission (%): 0.250 ±0.043% @ 546nm
Type: Neutral Density Filter
Width (mm): 50.00
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Reach 223: Compliant
Certificate of Conformance: View