


# SCHOTT NG9, 4.6 OD, 50mm Sq., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock #14-070 3-5 DAYS

- 1 + **A\$148.80**

ADD TO CART

Qty 1-10

A\$148.80

Qty 11+

A\$131.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Dimensions (mm):  
50.0 x 50.0

Optical Density OD (Average):  
4.6 ±0.07 @ 546nm

Glass/Filter Number:  
[SCHOTT NG9](#)

Length (mm):

|                                                      |
|------------------------------------------------------|
| 50.00                                                |
| <b>Coating:</b><br>Uncoated                          |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.51 |
| <b>Surface Quality:</b><br>60-40                     |
| <b>Transformation Temperature (°C):</b><br>470       |
| <b>Thickness (mm):</b><br>3.30                       |
| <b>Thickness Tolerance (mm):</b><br>(nominal)        |
| <b>Transmission (%):</b><br>0.003 ±0.00043% @ 546nm  |
| <b>Type:</b><br>Neutral Density Filter               |
| <b>Width (mm):</b><br>50.00                          |
| <b>Parallelism (arcmin):</b><br>≤3                   |
| <b>Dimensional Tolerance (mm):</b><br>±0.2           |
| <b>Wavelength Range (nm):</b><br>400 - 700           |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Reach 223:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |