

SCHOTT RG695, 50mm Sq., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock #14-523 3-5 DAYS

- 1 +

A\$124.00

ADD TO CART

Qty 1-10
A\$124.00
Qty 11+
A\$121.60
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Cut-On Wavelength (nm): 695.00 ±6
Density (g/cm³):

2.76
Glass/Filter Number: SCHOTT RG695
Length (mm): 50.00
Coating: Uncoated
Color: Black
Passband Limit 1 λ_{p1} (nm): 780
Index of Refraction n_d : 1.54
Spectral Transmittance t_p (%): 96
Stopband Limit λ_s (nm): 610
Surface Quality: 60-40
Transformation Temperature (°C): 532
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: VIS
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.91
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View